## **Products for Testing Machined Parts**

## **Membrane Discs**

| Description  | Pore Size (µm) | Diameter (mm) | Qty/Pk | Catalogue No. |
|--|----------------|---------------|--------|---------------|
| Nylon Net Filters  | 160            | 47            | 100    | NY6H04700     |
|  | 10             | 47            | 100    | NY1104700     |
|  | 40             | 47            | 100    | NY4004700     |
| Isopore™ Membrane,<br>polycarbonate, hydrophilic                 | 8              | 47            | 100    | TETP04700     |
| Mitex™ Membrane, PTFE,<br>hydrophobic                            | 10             | 47            | 100    | LCWP04700     |
| MF-Millipore Membrane,<br>mixed cellulose esters,<br>hydrophilic | 8              | 47            | 100    | SCWP04700     |
|  | 5              | 47            | 100    | SMWP04700     |
|  | 3              | 47            | 100    | SSWP04700     |



For a complete list of membranes, please contact technical service or visit www.millipore.com/membrane/mrc3/membranehome.

## Filterjet™ Solvent Dispenser, 25 mm

Use to spray a concentrated jet of ultraclean solvent or rinse solution on surfaces for cleaning. Filter holder, XX4002500, which is part of the dispenser, can also be used by itself for in-line pressure filtration of gases.

| Description                        | Catalogue No. |
|------------------------------------|---------------|
| Filterjet Solvent Dispenser, 25 mm | XX6702500     |
|                                    |               |
|                                    |               |
|                                    |               |



## Hydrosol™ Stainless Steel Filter Holder

Particulate or biological contamination analysis via vacuum filtration. Includes grounding set for use with flammable liquids. Filter holder is not autoclavable with filter in place.

| Description  | Catalogue No. |  |
|--|---------------|--|
| Hydrosol Stainless Steel Filter Holder<br>(For 47 mm disc filters) | XX2004720     |  |

